



WBP4S

Premiere 10A DP horz 4 gang GPO

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Insertion depth	0 mm
Height	78 mm
Width	211 mm

Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	4
-------------------------------------	---

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	premiere
------------------	----------