



WBP4S

### Premiere 10A DP horz 4 gang GPO

#### Technical properties

##### Configuration

Number of modules 4

##### Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

##### Electric current

Rated current 10 A

##### Dimensions

Insertion depth 0 mm

Height 78 mm

Width 211 mm

##### Installation, mounting

Entries cable entries bevelled

Mounting type flush-mounted

Installation mode for screw fastening

##### Connection

Type of connection with screw terminals

##### Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

##### Equipment

Number of socket outlets switchable 4

##### Identification

Main design line premiere