



WBQP115S

## FIN Single GPO 15A

### Technical properties

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

#### Electric current

Rated current 15 A

#### Installation, mounting

Installation mode for screw fastening

#### Connection

Type of connection with screw terminals

#### Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

#### Equipment

Number of socket outlets switchable 1