



WBQP115S-MB



## **FIN Single GPO 15A MB**

### **Technical properties**

#### **Electric current**

Rated current	15 A
---------------	------

#### **Frequency**

Frequency	50 - 50 Hz
-----------	------------

#### **Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

#### **Connectivity**

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

#### **Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

#### **Materials**

Colour	Black
--------	-------

#### **Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

#### **Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

#### **Accessories**

Has labelling field	No
---------------------	----

#### **Capacity**

Number of modules	1
-------------------	---

#### **Texts**

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Type of connection	With screw terminals
--------------------	----------------------

Related Series	finesse
----------------	---------