



WBQP115S-MW

FIN Single GPO 15A MW

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	15 A
---------------	------

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Safety

REACH conform	Yes
RoHS conform	Yes