



WBQP2S



FIN DGPO 10A

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Dimensions

Height	82 mm
Width	120 mm

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals
Related Series	finesse