



WBQP2S

FIN DGPO 10A

Technical properties

Configuration

Number of modules 2

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 10 A

Materials

Colour white

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

Equipment

Number of socket outlets switchable 2

With transparent product label holder No

Safety

Protection index IP IP20

Protection Enhanced contact protection