



WBQP2S-MB

FIN DGPO 10A MB

Technical properties

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Safety

Impact resistance IK IK08

Ingress Protection (IP) class IP20

Dimensions

Height 82 mm

Width 120 mm

Materials

Colour Black

Surface finish Matt

Material Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 2

Texts

Imprint Without imprint

Cover	Full cover plate
Protection	Enhanced contact protection
Related Series	finesse
