



WBQP2XS-MB

FIN DGPO 10A with Extra Switch MB

Technical properties

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour Black

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

Capacity

Number of modules 2

Texts

Cover Full cover plate

Related Series finesse