



WBQSA1-MW



## **FIN Architrave 1 gang MW**

### **Technical properties**

#### **Electric current**

Rated current	16 A
---------------	------

#### **Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

#### **Voltage**

Rated voltage	250 V
---------------	-------

#### **Frequency**

Frequency	50 - 50 Hz
-----------	------------

#### **Materials**

Colour	White
--------	-------

#### **Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### **Connectivity**

Mounting type	Screw mounting
---------------	----------------

#### **Controls and indicators**

Number of buttons	1
-------------------	---

#### **Texts**

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-way, with loop terminal
-------------	---------------------------