



WBQSA2



## FIN Architrave 2 gang

### Technical properties

#### Electric current

Rated current	16 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	White
--------	-------

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	2
-------------------	---

#### Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

#### Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal