



WBQSA2

FIN Architrave 2 gang

Technical properties

Electric current

Rated current 16 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal