



WBQSA3



FIN Architrave 3 gang

Technical properties

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

Texts

| | |
|-------------------|---------------------|
| Installation mode | For screw fastening |
|-------------------|---------------------|

| | |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

| | |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

| | |
|-------------|---------------------------|
| Switch mode | 2-way, with loop terminal |
|-------------|---------------------------|