



WBQSV6

FIN 6 Gang Switch Plate cw mechs

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Controls and indicators

Number of buttons	6
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	16 AX (200 W Self Ballasted Lamp (SBL))
---------------	---

Dimensions

Height	117 mm
Width	77 mm

Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Terminal	terminals accommodate 4 x 1.5 mm ² cable
----------	---

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Main design line	Finesse
------------------	---------