



WBSA1

Technical properties

Architecture

| | |
|----------------------|--------|
| Type of control unit | rocker |
|----------------------|--------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|-------------|
| Nominal voltage | 250 V AC |
| Rated voltage | 250 V AC/DC |
| Frequency | 50 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 16 AX |
|---------------|-------|

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
| Width | 36 mm |

Installation, mounting

| | |
|-------------------|---------------------|
| Mounting type | flush-mounted |
| Installation mode | for screw fastening |

Connection

| | |
|----------|---|
| Terminal | terminals accommodate 4 x 1.5 mm ² cable |
|----------|---|

Scope of delivery

| | |
|-------------------|---|
| Scope of delivery | supplied with tapered point 12 mm fixing screws ; supplied with both a premiere and a visage cover |
|-------------------|---|

Identification

| | |
|------------------|----------|
| Main design line | premiere |
|------------------|----------|