



WBSA2

Premiere 2G architrave switch

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Controls and indicators

Number of buttons	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Rated voltage	250 V AC/DC
Frequency	50 Hz

Electric current

Rated current	16 AX
---------------	-------

Dimensions

Height	85 mm
Width	36 mm

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Terminal	terminals accommodate 4 x 1.5 mm ² cable
----------	---

Scope of delivery

Scope of delivery	supplied with tapered point 12 mm fixing screws ; supplied with both a premiere and a visage cover
-------------------	---

Identification

Main design line	premiere
------------------	----------