

WBSA3-BK

### 3 Gang Architrave Switch Black

#### Technical properties

##### Electric current

Rated current 16 A

##### Installation, mounting

Mounting on Flush mounting

##### Voltage

Rated voltage 250 V

##### Frequency

Frequency 50 - 50 Hz

##### Materials

Colour Black

Surface finish Glossy

Material Polycarbonate (PC)

##### Identification

Assembly arrangement Basic element with full cover plate

##### Connectivity

Mounting type Screw mounting

##### Controls and indicators

Number of buttons 3

##### Safety

Ingress Protection (IP) class IP20

##### Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal