



WBSEV3

Silhouette 3G LP electronic Switch Vert

Technical properties

Controls and indicators

Number of buttons	3
-------------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Insertion depth	47 mm
Height	117 mm
Width	77 mm

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Cable

Cable length, extensions	max. 40 m
--------------------------	-----------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Use conditions

Operating temperature	5...40 °C
Storage/transport temperature	-20...60 °C