



WBSF3-BK

## 250V 75VA 3 Speed Fan Controller Black

### Technical properties

#### Architecture

Type of control unit	Rotative
----------------------	----------

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

#### Dimensions

Insertion depth	20 mm
Height	117 mm
Width	77 mm

#### Power

Max. output apparent power	75 W
----------------------------	------

#### Materials

Colour	black
--------	-------

#### Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

#### Connection

Terminal	terminals accommodate 4 x 1.5 mm <sup>2</sup> cable
----------	---

#### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

#### Safety

Protection index IP	IP20
RoHS conform	Yes

#### Identification

Appliance switch type	No
Main design line	premiere