



WBSP1R

Technical properties

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 10 A

Dimensions

Insertion depth 23 mm

Height 77 mm

Width 117 mm

Installation, mounting

Entries cable entries bevelled

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

Equipment

Number of socket outlets switchable 1

Safety

Protection Enhanced contact protection

Identification

Main design line silhouette