




WBSP2S



Silhouette 10A twin socket Horz+ shutter

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Dimensions

Built-in depth flush-mounted boxes	23 mm
Built-in depth	23 mm
Height	77 mm
Width	117 mm
Depth	33 mm

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

With lock	No
Accessories	
Has labelling field	No
Capacity	
Number of modules	2
Texts	
Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals
Cover, door	
Type of lid	Without lid
Related Series	silhouette