



WBSP2S-MB



## **SIL. 10A twin socket Horz+ shutter MB**

### **Technical properties**

#### **Electric current**

Rated current	10 A
---------------	------

#### **Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

#### **Frequency**

Frequency	50 - 50 Hz
-----------	------------

#### **Materials**

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC), Thermoplastic
Treatment	Varnished

#### **Dimensions**

Height	77 mm
Width	117 mm
Depth	33 mm
Built-in depth flush-mounted boxes	23 mm
Built-in depth	23 mm

#### **Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

#### **Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

#### **Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

#### **Accessories**

Has labelling field	No
---------------------	----

#### **Capacity**

Number of modules	2
-------------------	---

<b>Safety</b>	
Impact resistance IK	IK08
Ingress Protection (IP) class	IP20
<b>Functions</b>	
With orientation lighting	No
With function lighting	No
<b>Texts</b>	
Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals
Related Systems	silhouette