




WBSSV4



Silhouette 4G Switch Vert

Technical properties

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|----------------|--------------------|
| Colour | White |
| Surface finish | Glossy |
| Material | Polycarbonate (PC) |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 4 |
|-------------------|---|

Dimensions

| | |
|----------------|-------|
| Built-in depth | 23 mm |
|----------------|-------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|--------------------|---------------------------|
| Installation mode | For screw fastening |
| Type of connection | With screw terminals |
| Switch mode | 2-way, with loop terminal |