




WBSSV6



## Silhouette 6G Switch Vert

### Technical properties

#### Electric current

Rated current	16 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	6
-------------------	---

#### Dimensions

Built-in depth	23 mm
----------------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Switch mode	2-way, with loop terminal