




WBSSV6-MB



Technical properties

Electric current

Rated current 16 A

Installation, mounting

Mounting on Flush mounting

Frequency

Frequency 50 - 50 Hz

Materials

Colour Black

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 6

Dimensions

Built-in depth 23 mm

Safety

Ingress Protection (IP) class IP20

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal