



WBSV4

## Technical properties

### Architecture

Type of control unit	rocker
----------------------	--------

### Controls and indicators

Number of buttons	4
-------------------	---

### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

### Electric current

Rated current	16 AX
---------------	-------

### Dimensions

Insertion depth	16 mm
Height	117 mm
Width	77 mm

### Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

### Connection

Terminal	terminals accommodate 4 x 1.5 mm <sup>2</sup> cable
----------	---

### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

### Identification

Main design line	premiere
------------------	----------