



WBSV5

### Technical properties

#### Architecture

Type of control unit	rocker
----------------------	--------

#### Controls and indicators

Number of buttons	5
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

#### Electric current

Rated current	16 AX
---------------	-------

#### Dimensions

Insertion depth	16 mm
Height	117 mm
Width	77 mm

#### Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

#### Connection

Terminal	terminals accommodate 4 x 1.5 mm <sup>2</sup> cable
----------	---

#### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

#### Identification

Main design line	premiere
------------------	----------