



WBSV6

## Technical properties

### Architecture

Type of control unit	rocker
----------------------	--------

### Controls and indicators

Number of buttons	6
-------------------	---

### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

### Electric current

Rated current	16 AX
---------------	-------

### Dimensions

Insertion depth	16 mm
-----------------	-------

Height	117 mm
--------	--------

Width	77 mm
-------	-------

### Installation, mounting

Entries	cable entries bevelled
---------	------------------------

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

### Connection

Terminal	terminals accommodate 4 x 1.5 mm <sup>2</sup> cable
----------	---

### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

### Identification

Main design line	premiere
------------------	----------