



WBWSH2-BK

IP66 2G Switch 10A H W/Proof Black

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Controls and indicators

Number of buttons	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	25 mm
-----------------	-------

Height	77 mm
--------	-------

Width	117 mm
-------	--------

Materials

Colour	black
--------	-------

Colour	black
--------	-------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Type of connection	Screw connection
--------------------	------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Safety

Protection index IP	IP66
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----