



WBWSH3LFH-BK

**IP66 3G switch10A H Light/Fan/Heat Black**

**Technical properties**

**Architecture**

Type of control unit	rocker
----------------------	--------

**Controls and indicators**

Number of buttons	3
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Frequency	50 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	25 mm
Height	77 mm
Width	117 mm

**Materials**

Colour	black
Colour	black

**Installation, mounting**

Mounting type	flush-mounted
Installation mode	for screw fastening

**Connection**

Type of connection	with screw terminals
Type of connection	Screw connection

**Scope of delivery**

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

**Safety**

Protection index IP	IP66
---------------------	------