



WBWSV2-BK



IP66 Two Gang Switch 10A W/Proof Black

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Controls and indicators

Number of buttons	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	25 mm
Height	117 mm
Width	77 mm

Materials

Colour	black
Colour	black

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Safety

Protection index IP	IP66
REACH conform	Yes
RoHS conform	Yes