



WDI100



Touch Panel 10", Android

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Touch function	Yes
----------------	-----

Configuration

Category / ports	RJ45 Port for LAN connection
------------------	------------------------------

Connectivity

Connection	RJ45 cable in scope of delivery
Ethernet data rate	10/100 Mbit/s

Voltage

Auxiliary voltage	18...48 V DC
Power over Ethernet (PoE)	18...48 V DC

Dimensions

Assembling height	10 mm
-------------------	-------

Screen

TFT screen size	10 "
Display	yes

Storage

RAM	512 MB
-----	--------

Materials

RAL colour	RAL 7016 - Anthracite grey
Material	glass
Material family	Glass

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting
-------------------	--

Connection

Conductor cross-section (flexible), with wire end sleeve	0.75 mm ²
--	----------------------

Settings

Supported configuration modes	system
-------------------------------	--------

Equipment	
Text field	No
Light intensity	300 cd/m²
Processor	1 GHz
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	5...45 °C
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
Identification	
Composition	Control element
Main design line	KNX