



WDW070

IP20

## Housing flush-mounted for WDI07x

### Technical properties

#### Functions

Touch function No

#### Controls and indicators

Operation depending on the software visualisation one and two surface operation, stepless configuration based on sliding and page scrolling by swiping are supported

#### Connectivity

Connection RJ45 cable in scope of delivery

Connectors / jacks with USB/Mini USB type A adapter cable ; with RJ45 connector kit from connector and patch cable

#### Dimensions

Cavity wall opening (W x H x D) 190 x 126 x 47 mm

#### Power

Total power loss under IN 0 W

Dissipated energy in cable 0 W

#### Screen

Display no

#### Materials

Material family Metal

#### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting ; for vertical and horizontal mounting

#### Scope of delivery

Component Microphone and loudspeaker with echo suppression

#### Equipment

Interface type other

Text field No

Lighting Display illumination can be switched on automatically using brightness sensor

low noise silent, long-lasting convection cooling without fan

#### Safety

Protection with cleaning cover

#### Use conditions

Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
<b>Identification</b>	
Composition	other
Main design line	KNX