



10122114

**Frame 2gang, R.1, stainless steel/p. white**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Height	152.2 mm
Width	80.7 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Colour of design line	stainless steel/polar white
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material	stainless steel
Surface appearance	matt
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Main design line	Berker R.1
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---