



10122245

### Frame 2gang, R.3, black glossy

#### Technical properties

##### Dimensions

|        |           |
|--------|-----------|
| Depth  | 9.9 mm    |
| Height | 151.75 mm |
| Width  | 80.75 mm  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

##### Materials

|                           |                      |
|---------------------------|----------------------|
| Colour of labelling       | 217,217,217          |
| Colour of design line     | black                |
| Colour                    | black                |
| Colour                    | black                |
| RAL colour                | RAL 9005 - Jet black |
| Material                  | thermoplastic        |
| Material for printing     | PC-PMA black         |
| Type of surface treatment | untreated            |

##### Installation, mounting

|                   |   |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

##### Settings

|                   |            |
|-------------------|------------|
| Shading parameter | R1_czarny  |
| Laser parameter   | R1_schwarz |

##### Equipment

|                       |            |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

##### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

##### Instructions

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|