



10122349

**Frame 2gang, R.1, red trans./p. white glossy, acrylic**

**Technical properties**

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 152.2 mm |
| Width  | 81.2 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

**Materials**

|                              |                             |
|------------------------------|-----------------------------|
| Design lines special colours | red transparent/polar white |
| Colour                       | red                         |
| Colour                       | red                         |
| RAL colour                   | RAL 3003 - Ruby red         |
| Material / workmanship       | acrylic                     |
| Material                     | acrylic                     |
| Type of surface treatment    | untreated                   |

**Installation, mounting**

|                   |   |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
| Information text  | Not suitable for water-protected, flush-mounted installation IP44.  |