



10132045

### Frame 3gang, R.classic, black glossy

#### Technical properties

##### Dimensions

Depth	9.9 mm
Height	80.7 mm
Width	222.7 mm

##### Capacity

Number of sockets	3
-------------------	---

##### Materials

Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Surface appearance	glossy
Type of surface treatment	untreated

##### Installation, mounting

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

##### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

##### Identification

Main design line	Serie R.classic
------------------	-----------------

##### Instructions

Information text	Caution!In combinations, the spacer gland for Kaiser flush-mounted boxes must be used (order no. 1887).
------------------	---