



10132245

Frame 3gang, R.3, black glossy

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 222.7 mm |
| Width | 80.7 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

Materials

| | |
|---------------------------|--------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | black |
| Material for printing | PC-PMA black |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

Settings

| | |
|-------------------|------------|
| Shading parameter | R1_czarny |
| Laser parameter | R1_schwarz |

Equipment

| | |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|