



10132269

**Frame 3gang vert., lab. field, R.3, p. white glossy**

**Technical properties**

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 222.7 mm |
| Width  | 80.7 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| Colour of labelling       | 105,105,105           |
| Colour of design line     | polar white           |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Material for printing     | ASA polar white       |
| Surface appearance        | glossy                |
| Type of surface treatment | untreated             |

**Installation, mounting**

|                   |                 |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

**Settings**

|                   |          |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter   | R1_weiß  |

**Equipment**

|                       |            |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

**Use**

|  |                      |
|--|----------------------|
| Differentiation characteristic 1 - Sales | with labelling field |
|--|----------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

**Instructions**

|                  |  |
|------------------|--|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|--|