



10132339

**Frame 3gang, R.1, orange trans./p. white glossy, acrylic**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Height	223.2 mm
Width	81.2 mm

**Capacity**

Number of sockets	3
-------------------	---

**Materials**

Design lines special colours	orange transparent/polar white
Colour	orange
Colour	light orange
RAL colour	RAL 2003 - Pastel orange
Material / workmanship	acrylic
Material	acrylic
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	---

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Main design line	Berker R.1
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
Information text	Not suitable for water-protected, flush-mounted installation IP44.