



10136094

Frame 3gang Q.3 alu velvety, lacquered

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 80.7 mm |
| Width | 222.5 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

Materials

| | |
|------------------------|-----------|
| Material / workmanship | lacquered |
| Surface appearance | velvety |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |

Identification

| | |
|------------------|------------|
| Main design line | Berker Q.3 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|