



10142114

### Frame 4gang, R.1, stainless steel/p. white

#### Technical properties

##### Dimensions

Depth	9.9 mm
Height	294.2 mm
Width	81.2 mm

##### Capacity

Number of sockets	4
-------------------	---

##### Materials

Colour of design line	stainless steel/polar white
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material	stainless steel
Surface appearance	matt
Type of surface treatment	untreated

##### Installation, mounting

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	-------------------------------------------------------

##### Safety

Protection index IP	IP20
---------------------	------

##### Identification

Main design line	Berker R.1
------------------	------------

##### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---------------------------------------------------------------------------------------------------------------------------------