



10142145

Frame 4gang, R.1, black glossy

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 293.7 mm |
| Width | 80.7 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 4 |
|-------------------|---|

Materials

| | |
|---------------------------|----------------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | black |
| Colour | black |
| Colour | black |
| RAL colour | RAL 9005 - Jet black |
| Material | thermoplastic |
| Material for printing | PC-PMA black |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

Settings

| | |
|-------------------|------------|
| Shading parameter | R1_czarny |
| Laser parameter | R1_schwarz |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|