



10142209

### Frame 4gang, R.3, glass p. white

#### Technical properties

##### Dimensions

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 294.2 mm |
| Width  | 81.2 mm  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 4 |
|-------------------|---|

##### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour of design line     | glass polar white     |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Surface appearance        | glossy                |
| Type of surface treatment | untreated             |

##### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

##### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

##### Instructions

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|