



10142214

## Frame 4gang, R.3, stainless steel/p. white

### Technical properties

#### Dimensions

Depth	9.9 mm
Height	294.2 mm
Width	81.2 mm

#### Capacity

Number of sockets	4
-------------------	---

#### Materials

Colour of design line	stainless steel/polar white
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material	stainless steel
Surface appearance	matt
Type of surface treatment	untreated

#### Installation, mounting

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

Main design line	Berker R.3
------------------	------------

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---