



10142339

Frame 4gang, R.1, orange trans./p. white glossy, acrylic

Technical properties

Dimensions

Depth	9.9 mm
Height	294.2 mm
Width	81.2 mm

Capacity

Number of sockets	4
-------------------	---

Materials

Design lines special colours	orange transparent/polar white
Colour	orange
Colour	light orange
RAL colour	RAL 2003 - Pastel orange
Material / workmanship	acrylic
Material	acrylic
Type of surface treatment	untreated

Installation, mounting

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	---

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	Berker R.1
------------------	------------

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
Information text	Not suitable for water-protected, flush-mounted installation IP44.