



10152209

Frame 5gang, R.3, glass p. white

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 365.2 mm |
| Width | 81.2 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 5 |
|-------------------|---|

Materials

| | |
|---------------------------|-------------------------|
| Colour of design line | glass polar white |
| Colour | polarwhite |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | glass |
| Material / surface | metal, aluminum profile |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|