



10152245

Frame 5gang, R.3, black glossy

Technical properties

Dimensions

Depth	9.9 mm
Height	364.7 mm
Width	80.75 mm

Capacity

Number of sockets	5
-------------------	---

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Material / surface	metal, aluminum profile
Type of surface treatment	untreated

Installation, mounting

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	---

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	Berker R.3
------------------	------------

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---