



1311

Glass cover plate 1gang facet , TS, clear glossy

Technical properties

Dimensions

| | |
|--------------|--------|
| Depth | 5 mm |
| Screw length | 25 mm |
| Height | 160 mm |
| Width | 86 mm |

Materials

| | |
|-----------------------|--------|
| Colour of design line | clear |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; for screw fastening |
|-------------------|--|

Equipment

| | |
|----------|-------------------------------|
| Subplate | with polar white plastic base |
|----------|-------------------------------|

Safety

| | |
|-----------------|------|
| Impact strength | IK02 |
|-----------------|------|

Identification

| | |
|------------------|-----------|
| Main design line | Berker TS |
|------------------|-----------|