



13137006

Frame 1gang, K.1, ant. matt, lacq.

Technical properties

Dimensions

| | |
|-------------------------|-----------|
| Depth | 9.9 mm |
| Support plate thickness | max. 2 mm |
| Height | 80.5 mm |
| Width | 87 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|---------------------------|--------------------------|
| Colour of design line | anthracite |
| Colour | charcoal |
| Colour | anthracite charcoal grey |
| RAL colour | RAL 7021 - Black grey |
| Material / workmanship | lacquered |
| Material | thermoplastic |
| Surface appearance | matt |
| Type of surface treatment | Painted |

Installation, mounting

| | |
|-------------------|-------------------------------------------------------|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|-------------------------------------------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------|